

Garant

Side milling cutter with thread Width $a_p = 4$ mm, $\varnothing D$: 63mm



Order data

Order number	218540 63
GTIN	4045197849502
Item class	210

Description

Version:

Side milling cutters of robust special steel for reduced vibration.

Application:

For milling grooves and slots. For flat or non-flat slot base.

Note:

Side milling cutters available up to $\varnothing D = 200$ mm.

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size IP9**.

Technical description

$\varnothing D_2$	29 mm
Overall length L_{tot}	35 mm
maximum cutting depth $a_{e,max}$	14 mm
Cutting edge $\varnothing D_c$	63 mm
suitable indexable insert	SNHX
$\varnothing D_1$ h6	17 mm

Mounting thread M	M16
Number of effective inserts Z_{eff}	4
Number of indexable inserts	8
Width a_p	4 mm
Shank type	with thread
Through-coolant	no
Tool exchange	PowerCard
ISO code indexable insert	SN..1102
Pack of insert screws	219948 (IP9; 2.0 Nm)
Type of product	Side milling cutter

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 9IP	674252 9IP
Set of insert screws 10 pieces	219948
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2