



## Side milling cutter with thread Width $a_p = 5$ mm, $\varnothing D: 63$ mm

### Order data

Order number	218542 63_
GTIN	4045197849533
Item class	210

### Description

#### Version:

Side milling cutters of robust special steel for reduced vibration.

#### Application:

For milling grooves and slots.

Achievable base of the slot =  $176^\circ$  (not flat).

#### Note:

Use GARANT torque screwdriver TQ No. **211750 size 2.2**, with bit No. **674248 size TX9**.

Side milling cutters available up to  $\varnothing D = 200$  mm.

Through-coolant: false

Tool exchange: PowerCard

ISO code indexable insert: SN..1103

Pack of insert screws: 219949 (TX9; 2.0 Nm)

### Technical description

Pack of insert screws	219949 (TX9; 2.0 Nm)
Shank type	
Tool material	
ISO code indexable insert	SN..1103
Width $a_p$	5 mm
Tool exchange	PowerCard
Through-coolant	no
Machining strategy	
Norm	
Type of product	

