



Permanent magnetic circular chuck, with radial pole distribution, Chuck Ø: 150mm



Order data

Order number	380810 150
GTIN	4045197310910
Item class	33S

Description

Version:

- Neodymium magnet system for strong clamping force.
- Concentric grooves to assist component alignment.
- Centre is magnetically inactive, so that the plate can be bored through.

ON-OFF control by hand-operated lever.

Application:

- For grinding and turning.
- Particularly suitable for clamping annular components, due to radial pole distribution.
- For round and annular workpieces

Technical description

Weight	6.5 kg
Pitch circle Ø	80 / 120 mm
Nominal clamping force	100 N/cm ²
Centring hole depth	5 mm

Centre Ø	50 mm
Height tolerance	+0.5 / -2 mm
maximum boring-out Ø	24 mm
Chuck Ø	150 mm
Ø non-magnetic core	20 mm
Thread Ø	8×M6
Height	57 mm
Type of product	Magnetic clamping chuck