



Permanent magnetic clamping plate, transverse pole distribution, Pole area length: 600mm



Order data

Order number	380100 600
GTIN	4045197310668
Item class	33S

Description

Version:

- Neodymium magnet system for strong clamping force.
- ON-OFF control by hand-operated lever.
- In the OFF state a weak opposing field assists removal of the components.
- With longitudinal and transverse stops.
- Lamellae made of 3 mm brass / 12 mm steel.
- Magnetic field without straying, ensuring no magnetisation of tools.

Application:

- Suitable for heavy machining such as roughing.
- For small, medium, and large components even with rough or uneven surfaces.

Technical description

Grinding allowance in pole area	5 mm
Pole area length	600 mm
Weight	52 kg
Nominal clamping force	150 N/cm ²
Height	59 mm
Width	200 mm
Magnetic field height	12 mm

Height tolerance	+0.5 / -2 mm
Type of product	Magnetic clamping plate