

**Permanent magnetic circular chuck, with radial pole distribution, Chuck Ø: 200mm****Order data**

Order number	380810 200
GTIN	4045197310927
Item class	33S

Description**Version:**

- **Neodymium magnet system for strong clamping force.**
- **Concentric grooves to assist component alignment.**
- **Centre is magnetically inactive, so that the plate can be bored through.**

ON-OFF control by hand-operated lever.

Application:

- **For grinding and turning.**
- **Particularly suitable for clamping annular components, due to radial pole distribution.**
- **For round and annular workpieces**

Technical description

Centre Ø	60 mm
Height tolerance	+0.5 / -2 mm
Pitch circle Ø	110 / 180 mm
Ø non-magnetic core	28 mm

Nominal clamping force	100 N/cm ²
Weight	13 kg
Centring hole depth	5 mm
Thread Ø	8×M6
Chuck Ø	200 mm
maximum boring-out Ø	30 mm
Height	57 mm
Type of product	Magnetic clamping chuck