



## Internal micrometer Micromar, Measuring range: 6-8mm



### Order data

Order number	428900 6-8
GTIN	4059192010577
Item class	43A

### Description

#### Version:

Satin chrome-plated scales and operating parts.

Measuring spindle through-hardened and ground.

Quick drive with integral clutch.

Self-centring micrometer head from 12 mm with carbide measuring jaws.

From 12 mm **for measuring down to the bottom of the hole.**

From 40 mm the micrometer head is of aluminium, to save weight.

#### Optional extras:

Extension No. 428950, Setting rings No. 484030.

### Technical description

Measuring depth with extension	133 mm
Measuring range	6 - 8 mm
Standard measuring depth	58 mm
Dimension a	1.5 mm
Error limit	0.004 mm
Scale divisions	0.001 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

### Services

Calibration3-point internal micrometer maximum measuring range 20 mm	022500 20
DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200

### Accessories

Setting ringDIN 2250 C Nominal size $\varnothing$ 7 mm	484030 7
--	----------