




Permanent magnetic clamping plate, fine pole distribution, Pole area length: 450mm



Order data

Order number	380500 450
GTIN	4045197310712
Item class	33S

Description

Version:

- Neodymium magnet system for strong clamping force.
- Through transverse pole distribution.
- Uniform clamping force over entire width and side faces of the pole area.
- Lamellae made of 0.5 mm brass / 1.4 mm steel.

Application:

- For grinding and spark erosion machines.
- Universal clamping of small and medium-sized components of any thickness. (Particularly suitable for thin components).
- Consistent clamping force over entire width and side faces guaranteed.

Technical description

Grinding allowance in pole area	8 mm
Pole area length	450 mm
Width	150 mm
Weight	30 kg
Nominal clamping force	80 N/cm ²
Height tolerance	+0.5 / -2 mm

Height	51 mm
Magnetic field height	6 mm
Type of product	Magnetic clamping plate