

 Mahr**Internal micrometer Micromar, Measuring range: 8-10mm****Order data**

Order number	428900 8-10
GTIN	4059192010584
Item class	43A

**Description****Version:**

Satin chrome-plated scales and operating parts.

Measuring spindle through-hardened and ground.

Quick drive with integral clutch.

Self-centring micrometer head from 12 mm with carbide measuring jaws.

From 12 mm **for measuring down to the bottom of the hole.**

From 40 mm the micrometer head is of aluminium, to save weight.

**Optional extras:**

Extension No. 428950, Setting rings No. 484030.

**Technical description**

Measuring range	8 - 10 mm
Measuring depth with extension	133 mm
Dimension a	1.8 mm
Standard measuring depth	58 mm
Error limit	0.004 mm
Scale divisions	0.001 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

### Services

DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration3-point internal micrometer maximum measuring range 20 mm	022500 20

### Accessories

Setting ringDIN 2250 C Nominal size $\varnothing$ 9 mm	484030 9
--	----------