




## Permanent magnetic clamping plate, fine pole distribution, Pole area length: 600mm



### Order data

Order number	380500 600
GTIN	4045197310729
Item class	33S

### Description

#### Version:

- Neodymium magnet system for strong clamping force.
- Through transverse pole distribution.
- Uniform clamping force over entire width and side faces of the pole area.
- Lamellae made of 0.5 mm brass / 1.4 mm steel.

#### Application:

- For grinding and spark erosion machines.
- Universal clamping of small and medium-sized components of any thickness. (Particularly suitable for thin components).
- Consistent clamping force over entire width and side faces guaranteed.

### Technical description

Weight	52.4 kg
Pole area length	600 mm
Height	51 mm
Magnetic field height	6 mm
Width	200 mm
Height tolerance	+0.5 / -2 mm

Grinding allowance in pole area	8 mm
Nominal clamping force	80 N/cm <sup>2</sup>
Type of product	Magnetic clamping plate