

 Mahr**Internal micrometer Micromar, Measuring range: 85-100mm****Order data**

Order number	428900 85-100
GTIN	4059192010393
Item class	43A

Description**Version:**

Satin chrome-plated scales and operating parts.

Measuring spindle through-hardened and ground.

Quick drive with integral clutch.

Self-centring micrometer head from 12 mm with carbide measuring jaws.

From 12 mm **for measuring down to the bottom of the hole.**

From 40 mm the micrometer head is of aluminium, to save weight.

Optional extras:

Extension No. 428950, Setting rings No. 484030.

Technical description

Dimension a	0 mm
Standard measuring depth	97 mm
Measuring range	85 - 100 mm
Measuring depth with extension	247 mm
Error limit	0.005 mm
Scale divisions	0.005 mm
Standard	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

DAkkS calibration3-point internal micrometer maximum measuring range 200 mm	022510 200
Calibration3-point internal micrometer maximum measuring range 100 mm	022500 100

Accessories

Setting ringDIN 2250 C Nominal size \varnothing 90 mm	484030 90
---	-----------