

Mitutoyo**Internal micrometer Holtest, Measuring range: 40-50mm****Order data**

Order number	429000 40-50
GTIN	4946368517728
Item class	44A

Description**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. For through holes, measuring faces of hardened steel.

Optional extras:

Extensions No. 429010. Setting rings No. 484030.

Technical description

Barrel Ø	23 mm
Measuring range	40 - 50 mm
Dimension a	3.4 mm
Measuring depth with extension	248 mm
Standard measuring depth	98 mm
Overall length	140 mm
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box

Calibration	B6
Type of product	3-point internal micrometer

Services

Calibration 3-point internal micrometer maximum measuring range 50 mm	022500 50
DAkkS calibration 3-point internal micrometer maximum measuring range 200 mm	022510 200

Accessories

Setting ring DIN 2250 C Nominal size Ø 44 mm	484030 44
Setting ring DIN 2250 C Nominal size Ø 45 mm	484030 45
Setting ring DIN 2250 C Nominal size Ø 50 mm	484030 50
Extension for internal micrometer Type 3/150	429010 3/150
Setting ring DIN 2250 C Nominal size Ø 40 mm	484030 40
Setting ring DIN 2250 C Nominal size Ø 46 mm	484030 46
Setting ring DIN 2250 C Nominal size Ø 42 mm	484030 42