




## Polyamide coated steel measuring tape in a frame, Band length: 30m



### Order data

Order number	464900 30
GTIN	4007368045052
Item class	46M

### Description

#### Version:

**Capsule:** Indestructible plastic casing with soft finish surface. Storage is provided in the casing for the crank arm and the pull ring. Can be converted for left-hand use.

**Frame:** Light metal frame with ball bearing mounted fast winding and folding crank.

**Tape:** Patented tape start, **flextop coating**. Tape coating, made of transparent, highly flexible plastic, reliably prevents the tape from breaking at the start.

**Polyamide coated steel measuring tape.** Break-proof, with good flexibility. Non-buckling spring steel. **High abrasion resistance**, weather-proof and resistant to many chemicals and oils. With mm graduations throughout.

Sizes 20 and 30 with straight side pieces, size 50 with Vee side pieces.

#### Note:

Versions with 100 m length, or with inch graduations, or with start of scale type B / C available on request.

### Technical description

Tape width	13 mm
overall length	310 mm
Frame width	150 mm
Type of tape start	A
Band length	30 m

Standard	EG II
Calibration	G1
Type of product	Measuring tape

**Services**

CalibrationTape measure maximum length 50 m	026240 50
---	-----------