



## Surface comparison plates, Type: 107



### Order data

Order number	498861 107
GTIN	2050001052353
Item class	49K

### Description

#### Version:

The comparison plates contain the surface conditions for the most common types of machining. Wear-resistant and stainless.

#### Application:

For comparative checking of surface finishes using visual and tactile method (with finger nail).

Machining method: spark erosion

ISO roughness classes: N5 – N10

Comparison range Ra: 0.4 – 12.5 µm

Plate dimensions: 110×50 mm

Number of comparison patterns: 6

### Technical description

Machining method	spark erosion
Comparison range Ra	0.4 – 12.5 µm
Plate dimensions	110×50 mm
Number of comparison patterns	6
ISO roughness classes	N5 – N10
Type of product	Surface normal

## Services

Labellinglaser-etched Type

018940