



## HOLEX Pro Steel solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7 (mm or inch): 6,3



### Order data

|              |               |
|--------------|---------------|
| Order number | 122502 6,3    |
| GTIN         | 4045197830746 |
| Item class   | 12F           |

### Description

#### Version:

**Straight major cutting edges** and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Standard: DIN 6537 K

Tolerance nominal  $\varnothing$ : h7

Number of cutting edges Z: 2

Tolerance nominal  $\varnothing$ : h7

recommended maximum drilling depth  $L_2$ : 24.6 mm

Overall length L: 79 mm

Shank  $\varnothing D_s$ : 8 mm

Feed f in steel < 900 N/mm<sup>2</sup>: 0.18 mm/rev.

### Technical description

|  |            |
|--|------------|
| Nominal $\varnothing D_c$                | 6.3 mm     |
| Shank $\varnothing D_s$                  | 8 mm       |
| Number of cutting edges Z                | 2          |
| Standard                                 | DIN 6537 K |
| Overall length L                         | 79 mm      |
| recommended maximum drilling depth $L_2$ | 24.6 mm    |

|   |                   |
|---|-------------------|
| Tolerance nominal $\varnothing$         | h7                |
| Feed f in steel < 900 N/mm <sup>2</sup> | 0.18 mm/rev.      |
| Flute length L <sub>c</sub>             | 34 mm             |
| Series                                  | Pro Steel         |
| Coating                                 | TiAlN             |
| Tool material                           | Solid carbide     |
| Version                                 | 4xD               |
| Point angle                             | 140 °             |
| Shank                                   | DIN 6535 HB to h6 |
| Through-coolant                         | no                |
| Machining strategy                      | HPC               |
| Semi-Standard                           | yes               |
| Colour ring                             | green             |
| Type of product                         | Jobber drill      |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm <sup>2</sup>  | suitable                                  | 115 m/min      | P        |
| Steel < 750 N/mm <sup>2</sup>  | suitable                                  | 105 m/min      | P        |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  | 85 m/min       | P        |
| Steel < 1100 N/mm <sup>2</sup> | suitable                                  | 80 m/min       | P        |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  | 60 m/min       | P        |
| INOX < 900 N/mm <sup>2</sup>   | suitable                                  | 30 m/min       | M        |
| INOX > 900 N/mm <sup>2</sup>   | suitable only under restricted conditions | 25 m/min       | M        |
| GG                             | suitable                                  | 90 m/min       | K        |
| GGG                            | suitable                                  | 55 m/min       | K        |
| wet maximum                    | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |

