

**HOLEX**
**HOLEX Pro Steel solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7 (mm or inch): 9,4**

**Order data**

Order number	122502 9,4
GTIN	4045197831057
Item class	12F

**Description**
**Version:**

**Straight major cutting edges** and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Standard: DIN 6537 K

Tolerance nominal  $\varnothing$ : h7

Number of cutting edges Z: 2

Tolerance nominal  $\varnothing$ : h7

recommended maximum drilling depth  $L_2$ : 32.9 mm

Overall length L: 89 mm

Shank  $\varnothing D_s$ : 10 mm

Feed f in steel < 900 N/mm<sup>2</sup>: 0.22 mm/rev.

**Technical description**

Feed f in steel < 900 N/mm <sup>2</sup>	0.22 mm/rev.
Standard	DIN 6537 K
recommended maximum drilling depth $L_2$	32.9 mm
Overall length L	89 mm
Nominal $\varnothing D_c$	9.4 mm

Tolerance nominal $\varnothing$	h7
Shank $\varnothing D_s$	10 mm
Number of cutting edges Z	2
Flute length $L_c$	47 mm
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Version	4xD
Point angle	140°
Shank	DIN 6535 HB to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	115 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	105 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	85 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	25 m/min	M
GG	suitable	90 m/min	K
GGG	suitable	55 m/min	K
wet maximum	suitable		

dry

suitable