



## Rough grinding disc PREMIUM\*\*\*, Disc Ø×disc width: 125X7mm



### Order data

Order number	560405 125X7
GTIN	9003170053167
Item class	53T

### Description

#### Version:

**Special type** for working **non ferrous metals** such as aluminium, brass, bronze etc.

**Specification: A36L-BFX.**

- **Grit, bonding, abrasive additives** as well as reinforcement of the rough grinding discs are optimised for maximum metal removal rate and working life in their respective applications.
- **Shapes:** Rough grinding discs, depressed centres (shapes 27, 28, 29)
- **Grinding angle** 20° to 30°
- **Application:** On electric and pneumatic angle grinders with maximum 80 m/s circumferential speed for grinding welds, surfaces, and edges.

### Technical description

Disc thickness	7 mm
Bore Ø	22.23 mm
maximum speed	12200 min <sup>-1</sup>
Disc Ø	125 mm

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	20-30 degrees
optimised for material	Aluminium
optimised for material	Non-ferrous metals
maximum circumferential speed	80 m/s
Type of product	Rough grinding wheel

### User data

	Suitability	$V_c$	ISO code
Alu Mg	suitable		
CuZn	suitable		
dry	suitable		