



Rough grinding disc PREMIUM***, Disc Ø×disc width: 178X7mm



Order data

Order number	560405 178X7
GTIN	9003175760503
Item class	53T

Description

Version:

Special type for working **non ferrous metals** such as aluminium, brass, bronze etc.

Specification: A36L-BFX.

- **Grit, bonding, abrasive additives** as well as **reinforcement of the rough grinding discs** are **optimised for maximum metal removal rate and working life in their respective applications.**
- **Shapes: Rough grinding discs, depressed centres (shapes 27, 28, 29)**
- **Grinding angle 20° to 30°**
- **Application: On electric and pneumatic angle grinders with maximum 80 m/s circumferential speed for grinding welds, surfaces, and edges.**

Technical description

Bore Ø	22.23 mm
Disc thickness	7 mm
maximum speed	8500 min ⁻¹
Disc Ø	178 mm

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	20-30 degrees
optimised for material	Aluminium
optimised for material	Non-ferrous metals
maximum circumferential speed	80 m/s
Type of product	Rough grinding wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
CuZn	suitable		
dry	suitable		