

Garant
Burr Z7 – medium, diamond cut, Carbide, Type: M0618

Order data

Order number	540200 M0618
GTIN	4045197155108
Item class	51D

Description
Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Pointed cone shape**(SKM).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Cone

Head Ø: 6 mm

Head length L₁: 18 mm

Overall length: 50 mm

Shank Ø: 6 mm

Technical description

Shape	M0618
Toothing grit designation	medium
Shape description	Cone
Overall length	50 mm
Tooth type abbreviation	Z7
Head length L ₁	18 mm

Type of cut	staggered teeth
Shank Ø	6 mm
Head Ø	6 mm
Tool material	Carbide
Type of product	Burr