

Garant
Burr Z7 – medium, diamond cut, Carbide, Type: A0616

Order data

Order number	540200 A0616
GTIN	4045197154828
Item class	51D

Description
Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape A (ZYA), without end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Cylindrical without end cut

Head Ø: 6 mm

Head length L₁: 16 mm

Overall length: 50 mm

Shank Ø: 6 mm

Technical description

Overall length	50 mm
Shape description	Cylindrical without end cut
Shape	A0616
Toothing grit designation	medium
Tooth type abbreviation	Z7
Type of cut	staggered teeth

Head Ø	6 mm
Head length L ₁	16 mm
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr