



Rough grinding disc PREMIUM***, Disc Ø×disc width: 115X7mm



Order data

Order number	560300 115X7
GTIN	9003171170658
Item class	53T

Description

Version:

Special type for finishing CrNi steels. Best metal removal rates also on steel.

Specification: A30R-BFX.

- **Grit, bonding, abrasive additives as well as reinforcement of the rough grinding discs are optimised for maximum metal removal rate and working life in their respective applications.**
- **Shapes: Rough grinding discs, depressed centres (shapes 27, 28, 29)**
- **Grinding angle 20° to 30°**
- **Application: On electric and pneumatic angle grinders with maximum 80 m/s circumferential speed for grinding welds, surfaces, and edges.**

Technical description

Disc thickness	7 mm
maximum speed	13300 min ⁻¹
Bore Ø	22.23 mm
Disc Ø	115 mm

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	20-30 degrees
optimised for material	INOX
maximum circumferential speed	80 m/s
Type of product	Rough grinding wheel

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		