

Garant
Burr Z7 – medium, diamond cut, Carbide, Type: C1020

Order data

Order number	540200 C1020
GTIN	4045197154941
Item class	51D

Description
Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball nose

Head Ø: 10 mm

Head length L₁: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

Technical description

Shape description	ball nose
Toothing grit designation	medium
Overall length	60 mm
Type of cut	staggered teeth
Head Ø	10 mm
Head length L ₁	20 mm

Shape	C1020
Tooth type abbreviation	Z7
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr