

Garant

Burr Z7 – medium, diamond cut, Carbide, Type: A1625



Order data

Order number	540200 A1625
GTIN	4045197154866
Item class	51D

Description

Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape (ZYA), without end cut.**

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: Cylindrical without end cut

Head Ø: 16 mm

Head length L₁: 25 mm

Overall length: 65 mm

Shank Ø: 6 mm

Technical description

Shape	A1625
Overall length	65 mm
Shape description	Cylindrical without end cut
Head length L ₁	25 mm
Toothing grit designation	medium
Head Ø	16 mm

Tooth type abbreviation	Z7
Type of cut	staggered teeth
Shank Ø	6 mm
Tool material	Carbide
Type of product	Burr