

Garant**Felt polishing point Shank Ø 6 mm, Type: 167****Order data**

Order number	552200 167
GTIN	4045197240040
Item class	51E

Description**Version:**

Long-lived felt polishing point with **medium-hard felt which keeps its shape especially well.**

Application:

For rough polishing and high-gloss finish polishing of ground surfaces where there is a strict requirement for maintaining the exact geometrical shapes.

Note:

Felt polishing points must be used in conjunction **with grinding and polishing pastes** such as No. 552250 / 552330 / 552340 / 555740. Recommended circumferential speed 5 -10 m/s.

Technical description

Head Ø	10 mm
Shank Ø	6 mm
Head length	15 mm
Degree of hardness	medium
recommended circumferential speed	5 - 10 m/s

Type of product

Polishing points