



White steel measuring tape in a frame, Band length: 30m



Order data

Order number	464500 30
GTIN	4007368002987
Item class	46M

Description

Version:

Capsule: Indestructible plastic casing with soft finish surface. Storage is provided in the casing for the crank arm and the pull ring. Can be converted for left-hand use.

Frame: Light metal frame with ball bearing mounted fast winding and folding crank.

Tape: Patented tape start, **flextop coating**. Tape coating, made of transparent, highly flexible plastic, reliably prevents the tape from breaking at the start.

White steel measuring tape. Hardened tape, phosphated coating provides corrosion resistance, with wear-resistant synthetic resin coating. Good legibility. With mm graduations throughout. Sizes 20 and 30 with straight side pieces, size 50 with Vee side pieces.

Note:

Versions with 100 m length, or with inch graduations, or with start of scale type B / C available on request.

Technical description

overall length	310 mm
Frame width	120 mm
Tape width	13 mm
Type of tape start	A
Band length	30 m

Standard	EG II
Calibration	G1
Type of product	Measuring tape

Services

CalibrationTape measure maximum length 50 m	026240 50
---	-----------