

Burr, coated Z7 – medium, diamond cut, Carbide TiAlN, Type: C1225



Order data

Order number	540260 C1225
GTIN	4027497038831
Item class	56L

Description

Version:

Shank Ø 6 mm.

LUKAS burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge stability, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Additional TiAIN coating for longer working life and temperature resistance.

For high thermal and mechanical loadings (Heavy Duty). **Cylindrical ball nose shape** (WRC)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: ball nose

Head Ø: 12 mm

Head length L₁: 25 mm Overall length: 65 mm

Shank Ø: 6 mm

Technical description

Type of cut	staggered teeth
Overall length	65 mm
Shape	C1225
Tooth type abbreviation	Z7

Head length L₁	25 mm
Shape description	ball nose
Toothing grit designation	medium
Head Ø	12 mm
Shank Ø	6 mm
Tool material	Carbide TiAIN
Coating	TiAlN
Type of product	Burr