Lucăs Burr, coated Z7 – medium, diamond cut, Carbide TiAlN, Type: D0605



Order data

Order number	540260 D0605
GTIN	4027497040223
Item class	56L

Description

Version:

Shank Ø 6 mm.

LUKAS burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge stability, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Additional TiAIN coating for longer working life and temperature resistance.

For high thermal and mechanical loadings (Heavy Duty). Ball shape (KUD)

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm Shape description: ball Head Ø: 6 mm Head length L_1 : 5 mm Overall length: 50 mm Shank Ø: 6 mm

Technical description

Tooth type abbreviation	Ζ7
Type of cut	staggered teeth
Overall length	50 mm
Shape	D0605

Head length L ₁	5 mm
Shape description	ball
Head Ø	6 mm
Toothing grit designation	medium
Shank Ø	6 mm
Tool material	Carbide TiAIN
Coating	TiAIN
Type of product	Burr