

Burr, coated Z7 - medium, diamond cut, Carbide TiAlN, Type: F1225



Order data

Order number	540260 F1225
GTIN	4027497047765
Item class	56L

Description

Version:

Shank Ø 6 mm.

LUKAS burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge stability, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Additional TiAIN coating for longer working life and temperature resistance.

For high thermal and mechanical loadings (Heavy Duty). **Round arch shape** (RBF).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: round arch

Head Ø: 12 mm

Head length L₁: 25 mm Overall length: 65 mm

Shank Ø: 6 mm

Technical description

Head length L₁	25 mm
Shape description	round arch
Overall length	65 mm
Type of cut	staggered teeth

Toothing grit designation	medium
Shape	F1225
Head ∅	12 mm
Tooth type abbreviation	Z7
Shank Ø	6 mm
Tool material	Carbide TiAIN
Coating	TiAIN
Type of product	Burr