



## White steel tape measure in a frame, Band length: 50m



### Order data

Order number	464500 50
GTIN	4007368004011
Item class	46M

### Description

#### Version:

**Capsule:** Indestructible plastic casing with soft finish surface. Storage is provided in the casing for the crank arm and the pull ring. Can be converted for left-hand use.

**Frame:** Light metal frame with ball bearing mounted fast winding and folding crank.

**Tape:** Patented tape start, **flextop coating**. Tape coating, made of transparent, highly flexible plastic, reliably prevents the tape from breaking at the start.

**White steel tape measure.** Hardened tape, phosphated coating provides corrosion resistance, with wear-resistant synthetic resin coating. Good legibility. With mm graduations throughout. Sizes 20 and 30 with straight side pieces, size 50 with Vee side pieces.

#### Note:

Versions with 100 m length, or with inch graduations, or with start of scale type B / C available on request.

Calibration: G1

Standard: EG II

Tape width: 13 mm

Type of tape start: A

overall length: 340 mm

Frame width: 150 mm

### Technical description

Tape width	13 mm
overall length	340 mm

Frame width	150 mm
Type of tape start	A
Band length	50 m
Standard	EG II
Calibration	G1
Type of product	Measuring tape

### Services

Calibration Locking tape measure maximum length 50 m	016140 50
Labelling laser-etched Type	018940
Calibration Tape measure maximum length 50 m	026240 50
DAkkS Calibration locking tape measure 50	026250 50