

## Garant

### Burr Z7 – medium, diamond cut, Carbide, Type: F0618



#### Order data

Order number	540350 F0618
GTIN	4045197609847
Item class	51D

#### Description

##### Version:

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

**Shank length 200 mm** (can be cut to length).

Shank Ø 6 mm. **Round arch shape F** (RBF).

##### Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Do not start the machine until the burr is inside the component.

Shank Ø: 6 mm

Shape description: round arch

Head Ø: 6 mm

Head length: 18 mm

Overall length: 218 mm

Shank Ø: 6 mm

#### Technical description

Shape description	round arch
Type of cut	staggered teeth
Head Ø	6 mm
Tooth type abbreviation	Z7
Toothing grit designation	medium

Overall length	218 mm
Shape	Round arch
Shank Ø	6 mm
Head length	18 mm
Tool material	Carbide
Type of product	Burr

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		