

Garant
Solid carbide torus cutter, uncoated, Ø h6 DC / R1: 8/2,0mm

Order data

Order number	206192 8/2,0
GTIN	4045197853103
Item class	11X

Description
Version:

Eccentric relief ground, additionally **polish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium workpieces.

Tolerances:

- **Corner radius**

$R_1 = 0.5$ tolerance ± 0.02 .

$R_1 > 0.5 - 1.5$ tolerance ± 0.03 .

$R_1 > 1.5$ tolerance ± 0.05 .

Dimensions to manufacturer's standard.

Technical description

Recess Ø D_1	7.4 mm
Feed f_z for copy milling in short-chipping aluminium	0.04 mm
Overall length L	100 mm
Shank	DIN 6535 HA to h6
Feed f_z for side milling in short-chipping aluminium	0.04 mm
Shank Ø D_s	8 mm
Overhang length L_1 incl. recess	62 mm
Balance quality with shank	G 2.5 with HA
Cutting edge Ø D_c	8 mm
Corner radius R_1	2 mm

No. of teeth Z	3
Flute length L _c	13 mm
Helix angle	45 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Tolerance nominal Ø	h6
Direction of infeed	horizontal, oblique and vertical
Cutting width a _e for milling operation	0.05×D for copy milling
Cutting width a _e for milling operation	0.3×D for side milling
Through-coolant	no
Shank tolerance	h6
Colour ring	yellow
Type of product	Torus cutter

User data

	Suitability	V _c	ISO code
Aluminium	Suitable	130 m/min	N
Aluminium (short chipping)	suitable	100 m/min	N
Alu > 10% Si	suitable	80 m/min	N
PMMA acrylic	Suitable	130 m/min	N
PE-HD	Suitable	90 m/min	N
PA 66	Suitable	100 m/min	N
PEEK	Suitable	90 m/min	N
PF 31	Suitable	80 m/min	N
Cu	Suitable	70 m/min	N
CuZn	Suitable	90 m/min	N

wet maximum	suitable
wet minimum	Suitable only under restricted conditions
dry	suitable only under restricted conditions
Air	suitable only under restricted conditions
Services	
Shank grinding Type HB	129100 HB