

**DCGT 11T301, Grade: PDL025****Order data**

Order number	260384 PDL025
GTIN	
Item class	25E

Description**Technical description**

Corner radius	0.1 mm
Chip breaker	MFP-SK
Cutting conditions	slightly interrupted
Cutting speed v_c main application	100 - 300 m/min
Grade	PDL025
Cutting depth a_p	0.5 - 2.5 mm
Main application	N
Feed f	0.03 - 0.15 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DCGT 11T301

Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning