

Mitutoyo**Internal micrometer set Holtest for measuring blind holes, Measuring range: 20-50mm****Order data**

Order number	429055 20-50
GTIN	4946368517599
Item class	44A

Description**Version:**

Stainless, all reading parts glare-free satin chrome-plated. Barrel with jet black scale and ratchet. Blind hole version. **Measuring faces of hardened steel with titanium coating for long tool life.**

Supplied with:

Internal micrometers No. 429005. Setting rings similar to No. 484030, extension 150 mm No. 429010.

Technical description

Setting ring \varnothing	25 / 40 mm
Measuring range	20 - 50 mm
Number of micrometers	4
Error limit	0.006 mm
Scale divisions	0.005 mm
Standard	Manufacturer's standard
Micrometer barrel graduations	1/50 mm

Measurement technology	analogue
Packaging	sturdy box
Calibration	S6
Type of product	3-point internal micrometer

Services

Calibration Internal micrometer set Measuring range 20-50 mm	020550 20-50
--	--------------

Accessories

Internal micrometer Holtestfor measuring blind holes Measuring range 20-25 mm	429005 20-25
Internal micrometer Holtestfor measuring blind holes Measuring range 30-40 mm	429005 30-40
Setting ring DIN 2250 C Nominal size Ø 45 mm	484030 45
Setting ring DIN 2250 C Nominal size Ø 35 mm	484030 35
Setting ring DIN 2250 C Nominal size Ø 27 mm	484030 27
Internal micrometer Holtestfor measuring blind holes Measuring range 25-30 mm	429005 25-30
Internal micrometer Holtestfor measuring blind holes Measuring range 40-50 mm	429005 40-50
Extension for internal micrometer Type 3/150	429010 3/150
Setting ring DIN 2250 C Nominal size Ø 22 mm	484030 22