

**Garant**
**Solid carbide reamer HPC blind hole, TiAlN, Nominal  $\varnothing$  DC: 15mm**

**Order data**

Order number	164351 15
GTIN	4045197853356
Item class	10N

**Description**
**IMPORTANT: item is configurable**
 $\varnothing$  range: 14.21 - 15.2 mm, Intervall: 0,001

 Nominal  $\varnothing$  D<sub>C</sub>: 15 mm

**Version:**

**Version suitable for NC** with straight shank  $\varnothing$  for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

**Reamers finish ground to match your specifications.**

With short, straight flutes.

**Application:**

 For **HPC/HSC reaming** of **blind holes**.

**Note:**
**NEW GENERATION AVAILABLE!**
**Recommended successor product is No. 164425.**

Application for type of drilling: for blind holes

Number of cutting edges Z: 6

 $\varnothing$  range: 14.21 - 15.2 mm

 Flute length L<sub>C</sub>: 22 mm

 Overhang L<sub>1</sub>: 75 mm

Overall length L: 130 mm

Number of cutting edges Z: 6

 Shank  $\varnothing$  D<sub>s</sub>: 16 mm

**Technical description**

Shank tolerance	h6
-----------------	----

Ø range	14.21 - 15.2 mm
Flute length $L_c$	22 mm
Shank Ø $D_s$	16 mm
Overhang $L_1$	75 mm
Overall length $L$	130 mm
Number of cutting edges $Z$	6
Nominal Ø $D_c$	15 mm
Feed $f$ in stainless steel < 900 N/mm <sup>2</sup>	0.23 mm/rev.
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA to h6
Machining strategy	HPC
Application for type of drilling	for blind holes
Colour ring	blue
Type of product	Phillips bit

## User data

	Suitability	$V_c$	ISO code
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	25 m/min	M
Oil	suitable		
wet maximum	suitable		