



Knurl forming tool universal, Shank size: 16mm



Order data

Order number	290090 16
GTIN	4030741325106
Item class	29H

Description

Version:

Modular design: Can be used universally as right-hand or left-hand version.

Grub screws in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

Technical description

for knurl width w	6 mm
Shank height	16 mm
Shank width	16 mm
for knurl $\varnothing d_1$	15 mm
for knurl bore $\varnothing d_2$	6 mm
Working range	3 - 40 mm
for knurled countersunk $\varnothing d_3$	11 mm
Closure stud	299925 1

Disc	299927 1
Cutting direction	Left-hand and right-hand
for knurl profile	RAA 2×AA
Type of product	Self-centering knurling tool

Accessories

Disc Type 1	299927 1
Closure stud Type 1	299925 1