



Vernier caliper with spring-loaded thumb-lock, Measuring range: 150mm



Order data

Order number	410255 150
GTIN	4059192001575
Item class	43A

Description

Version:

Satin chromium plated anti-glare reading parts. Fine, high-contrast scale. Precision lapped measuring faces.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Measuring range	0 - 150 mm
Calibration	A1
Jaw length	40 mm
Packaging	sturdy box
Scale divisions	0.05 mm
Graduation	1/20 mm
Graduation	1/128 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3
Depth gauge available	yes
Measurement deviation E MPE	± 0.05 mm

Locking	Spring-loaded thumb-lock
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Table for calipers	412180
Synthetic leather case for vernier calipers	412500