

**Mahr****Vernier caliper with spring-loaded thumb-lock, Measuring range: 150mm****Order data**

Order number	410255 150
GTIN	4059192001575
Item class	43A

**Description****Version:**

Satin chromium plated anti-glare reading parts. Fine, high-contrast scale. Precision lapped measuring faces.

all parts: hardened

Standard: ISO 13385

Reversible reading: mm / inch

Depth gauge: rectangular 3.7×1.3

Packaging: sturdy box

Calibration: A1

Scale divisions: 0.05 mm

Graduation: 1/20 mm

Graduation: 1/128 in

Measurement deviation E MPE: ± 0.05 mm

Jaw length: 40 mm

**Technical description**

Measuring range	0 - 150 mm
Calibration	A1
Jaw length	40 mm
Packaging	sturdy box
Scale divisions	0.05 mm
Graduation	1/20 mm

Graduation	1/128 in
Reversible reading	mm / inch
Standard	ISO 13385
Depth gauge	rectangular 3.7×1.3
Depth gauge available	yes
Measurement deviation E MPE	± 0.05 mm
Locking	Spring-loaded thumb-lock
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

## Services

Calibration Calipers / depth gauges maximum measuring range 200 mm	011030 200
Labelling laser-etched Type	018940
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	011050 200
Calibration Calipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibration Calipers / depth gauges maximum measuring range 200 mm	021010 200

## Accessories

Table for calipers	412180
Synthetic leather case for vernier calipers	412500
Plastic case Type MS150	412470 MS150
Plastic case Type MS150	412468 MS150