

Garant**Burr Z7 – medium, diamond cut, Carbide, Type: C0616****Order data**

Order number	540350 C0616
GTIN	4045197222404
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Shank length 200 mm (can be cut to length).

Shank Ø 6 mm. **Shape C cylindrical ball nose** (WRC).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Do not start the machine until the burr is inside the component.

Shank Ø: 6 mm

Shape description: Ball nose

Head Ø: 6 mm

Head length: 16 mm

Overall length: 216 mm

Shank Ø: 6 mm

Technical description

Toothing grit designation	medium
Head Ø	6 mm
Type of cut	staggered teeth
Shape	Ball nose
Overall length	216 mm

Shape description	Ball nose
Tooth type abbreviation	Z7
Shank Ø	6 mm
Head length	16 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		