

Garant
Burr Z1 - coarse, Carbide, Type: AS0820

Order data

Order number	540600 AS0820
GTIN	4045197155740
Item class	51D

Description
Version:

 Shank \varnothing 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Cylindrical shape**(ZYAS), **with end cut**.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	AS0820
Shape description	Cylindrical with end cut
Toothing grit designation	coarse
Head \varnothing	8 mm
Tooth type abbreviation	Z1
Overall length	60 mm
Shank \varnothing	6 mm
Head length	20 mm
Series	Tooth configuration Z1
Tool material	Carbide

Type of product

Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
Wood	suitable only under restricted conditions		