

**HOLEX®**
**Tap wrench, adjustable, Type: 1.1/2**

**Order data**

Order number	148400 1.1/2
GTIN	4045197854919
Item class	12L

**Description**
**Version:**

With hardened jaws. Steel handles galvanised. For use in confined spaces one steel handle can be unscrewed.

**Standard use:**

body made of die-cast zinc.

Norm: DIN 1814

Capacity □: 2 - 7.5 mm

for hand taps DIN 352: M1 – M12

for hand reamer Ø DIN 206: 2.5 - 9.5 mm

Overall length: 175 mm

**Technical description**

for hand reamer Ø DIN 206	2.5 - 9.5 mm
Capacity □	2 - 7.5 mm
Overall length	175 mm
for hand taps DIN 352	M1 – M12
Norm	DIN 1814