

**HOLEX®**

## Tap wrench, adjustable, Type: 2



### Order data

Order number	148400 2
GTIN	4045197854964
Item class	12L

### Description

**Version:**

With hardened jaws. Steel handles galvanised. For use in confined spaces one steel handle can be unscrewed.

**Standard use:**

body made of die-cast zinc.

Norm: DIN 1814

Capacity □: 4 - 8.5 mm

for hand taps DIN 352: M4.5 – M12

for hand reamer Ø DIN 206: 5 - 10 mm

Overall length: 265 mm

### Technical description

Overall length	265 mm
for hand taps DIN 352	M4.5 – M12
for hand reamer Ø DIN 206	5 - 10 mm
Capacity □	4 - 8.5 mm
Norm	DIN 1814