

## Garant

**GARANT Master Steel FEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 10,8mm**



### Order data

Order number	123236 10,8
GTIN	4045197843135
Item class	11E

### Description

#### Version:

**3-flute drill**, specially developed for **use at very high feed rates**. Outstandingly suitable for machines with **high installed power** and stable machining conditions.

- **Special cutter geometry with stable cutting edges and large clearance at the centre enables very high feed rates.**
- **The patented tip is optimised for chip flow and generates low cutting pressure with good chip breakage.**

The **sector-leading technology of the drill point** guarantees **optimum self-centring behaviour**. 3 guide chamfers guarantee a stable exit from the hole and an exact roundness of the hole.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

For process reliability when using the 12xD deep-hole drill, an initial centre drilling with an NC spotting drill No. 121130 with **155° point angle** is necessary.

### Technical description

Number of cutting edges Z	3
Standard	Manufacturer's standard
Tolerance nominal Ø	h7
Shank Ø D <sub>s</sub>	12 mm
Overall length L	204 mm
Flute length L <sub>c</sub>	156 mm

Nominal $\varnothing D_c$	10.8 mm
recommended maximum drilling depth $L_2$	139.8 mm
Feed $f$ in steel $< 1100 \text{ N/mm}^2$	0.5 mm/rev.
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Version	12xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, to 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Steel $< 500 \text{ N/mm}^2$	suitable	120 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	110 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	100 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	90 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable	70 m/min	P
Steel $< 55 \text{ HRC}$	suitable	60 m/min	H
INOX $< 900 \text{ N/mm}^2$	suitable	55 m/min	M
INOX $> 900 \text{ N/mm}^2$	suitable	50 m/min	M
Ti $> 850 \text{ N/mm}^2$	suitable only under restricted conditions	40 m/min	S
GG	suitable	120 m/min	K
GGG	suitable	80 m/min	K

Uni	suitable
wet maximum	suitable
wet minimum	suitable