

HOLEX®**Tap wrench, adjustable, Type: 3****Order data**

| | |
|--------------|---------------|
| Order number | 148400 3 |
| GTIN | 4045197854988 |
| Item class | 12L |

Description**Version:**

With hardened jaws. Steel handles galvanised. For use in confined spaces one steel handle can be unscrewed.

Standard use:

body made of die-cast zinc.

Norm: DIN 1814

Capacity □: 4.9 - 12 mm

for hand taps DIN 352: M5 – M20

for hand reamer Ø DIN 206: 6.5 - 15 mm

Overall length: 370 mm

Technical description

| | |
|---------------------------|-------------|
| Overall length | 370 mm |
| for hand reamer Ø DIN 206 | 6.5 - 15 mm |
| for hand taps DIN 352 | M5 – M20 |
| Capacity □ | 4.9 - 12 mm |
| Norm | DIN 1814 |