

PLANOLITH
Machine test standard Axis-Inspect-Master, width×length: 800X600 mm


Order data

Order number	431882 800X600
GTIN	2050001949936
Item class	46H

Description

Version:

Rectangular shape of specially selected natural granite with weight-reducing holes and 12 reference holes (with ceramic sleeves).

Advantage:

Reduction in downtime due to machine stoppages. Saving on servicing costs.

Application:

Measurement and inspection tool for CNC machine tools, measuring machines or measuring arms. For quick testing of the machine geometry and positioning, e.g. after a crash.

Accuracy:

The 4 side faces are machined square and plane parallel to each other (2 µm). The front face is machined angular to the side faces. The exact positions of the 12 reference holes are recorded in the test certificate supplied.

Supplied with:

Transport packaging

Note:

Please note **additional carriage charge**.

Test certificate: Manufacturer's test certificate

Flatness of the front face: 0.01 mm

Flatness of the side faces: 0.002 mm

Right angle tolerance: 0.002 mm

Thickness: 70 mm

Weight: 90 kg

Technical description

Flatness of the front face	0.01 mm
Width	800 mm
Thickness	70 mm
Weight	90 kg
Length	600 mm
Flatness of the side faces	0.002 mm
Right angle tolerance	0.002 mm
Test certificate	Manufacturer's test certificate
Type of product	Machine test standard

Accessories

Care product for granite Contents 0,5 kg	431840 0,5
Cleaner for natural granite Contents 0,5 l	431841 0,5