

Garant

Solid carbide deburrer 30°, uncoated, Ø h6 DC: 16mm



Order data

Order number	208150 16
GTIN	4045197859266
Item class	11X

Description

Version:

Tolerance: **Dimension S = ±0.1 mm, point angle ±10 arc minutes.**

With special flute geometry for smooth cutting.

Application:

Perfectly suitable for **chamfering** and **deburring** component edges and for **contouring applications**.

Technical description

Overall length L	93 mm
Shank Ø D _s	16 mm
Shank	DIN 6535 HA with h6
Feed f _z in steel < 900 N/mm ²	0.08 mm
Dimension S	30 mm
No. of teeth Z	4
Cutting edge Ø D _c	16 mm
Corner chamfer angle	75 degrees
Chamfer mill	15 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard

Type	N
Tolerance nominal \varnothing	h6
Direction of infeed	horizontal and oblique
Countersink tip angle	30 degrees
Through-coolant	no
Shank tolerance	h6
Colour ring	without
Type of product	Deburrers

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	180 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	105 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	60 m/min	P
Steel < 900 N/mm ²	suitable	55 m/min	P
Steel < 1100 N/mm ²	suitable	35 m/min	P
INOX < 900 N/mm ²	suitable	40 m/min	M
INOX > 900 N/mm ²	suitable	30 m/min	M
GG(G)	suitable	55 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
Air	Suitable only under restricted conditions		

Services

Shank grinding Type HB

129100 HB