

Garant

GARANT Master Steel SPEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 4,9mm



Order data

| | |
|--------------|---------------|
| Order number | 123026 4,9 |
| GTIN | 4045197846204 |
| Item class | 11E |

Description

Version:

Developed for use with **very high cutting speeds**. Outstandingly suitable for machines with **low installed power** and high speeds.

- **Clear reduction in cutting forces due to special cutter geometry.**
- **Coating for best wear resistance even at high process temperatures.**
- **Polished flutes for good chip clearance.**

A **slim chisel point** and the **special arrangement of the 4 guide chamfers** ensure **high positioning and alignment accuracy**. Optimised micro-geometry for increased working life and performance capability.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

| | |
|--|-------------------------|
| Nominal Ø D_c | 4.9 mm |
| Flute length L_c | 57 mm |
| Shank Ø D_s | 6 mm |
| Tolerance nominal Ø | h7 |
| Standard | Manufacturer's standard |
| Number of cutting edges Z | 2 |
| Feed f in steel < 1100 N/mm ² | 0.1 mm/rev. |
| Overall length L | 95 mm |

| | |
|---|-------------------|
| recommended maximum drilling depth L ₂ | 49.7 mm |
| Series | Master Steel |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Version | 8×D |
| Point angle | 135 degrees |
| Shank | DIN 6535 HB to h6 |
| Through-coolant | yes, to 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm ² | suitable | 195 m/min | P |
| Steel < 750 N/mm ² | suitable | 150 m/min | P |
| Steel < 900 N/mm ² | suitable | 135 m/min | P |
| Steel < 1100 N/mm ² | suitable | 125 m/min | P |
| Steel < 1400 N/mm ² | suitable | 80 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 65 m/min | M |
| GG | suitable | 120 m/min | K |
| GGG | suitable | 115 m/min | K |
| Uni | suitable | | |
| wet maximum | suitable | | |
| wet minimum | suitable | | |