

## Garant

### Solid carbide end torus cutter HPC, TiAlN, Ø h9 DC: 5mm



#### Order data

Order number	206267 5
GTIN	4045197860712
Item class	11X

#### Description

##### Version:

Special centre cutting edge geometry for traverse milling at very high feed rates.

Tolerance: Corner radius  $R_1 = \pm 0.01$  mm.

##### Application:

**For copy and traverse milling** over the full range of hard machining **under HPC/HSC conditions**.

Using special milling strategies **very high rates of metal removal can be achieved**.

##### Note:

**Successor product to No. 206274.**

**Tools can be reground.**

#### Technical description

No. of teeth Z	4
Overall length L	100 mm
Feed $f_z$ in steel $< 900$ N/mm <sup>2</sup>	0.079 mm
Shank Ø $D_s$	6 mm
Cutting edge Ø $D_c$	5 mm
Flute length $L_c$	3.5 mm
Programming radius	0.5 mm
Recess Ø $D_1$	4.6 mm
Dimension $a_{p\ max}$ transverse	0.35 mm
Overhang length $L_1$ incl. recess	28 mm

Setting angle $\kappa$	9.5 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal $\varnothing$	h9
Helix angle	15 degrees
Direction of infeed	horizontal and oblique
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Shank	DIN 6535 HA to h5
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End torus mill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	130 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	125 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	115 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	M
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		

Air

suitable only under  
restricted conditions

**Services**

Shank grinding Type HB

129100 HB