

**Garant**
**GARANT Diabolo solid carbide end torus cutter HPC, TiAlN, Ø h9 DC: 6mm**

**Order data**

Order number	206273 6
GTIN	4045197860798
Item class	11X

**Description**
**Version:**
**GARANT Diabolo:**

Special geometry, coating and carbide for hard machining.

Tolerance: Corner radius  $R_1 = \pm 0.01$  mm.

Special centre cutting edge geometry for traverse milling at very high feed rates.

**Application:**

**For copy and traverse milling** in hard machining **under HPC / HSC conditions**. Special milling strategies allow **very high metal removal rates**.

**Note:**

**Successor product to No. 206276.**

**Tools can be reground.**

**Technical description**

Dimension $a_{p \max}$ transverse	0.2 mm
Flute length $L_c$	3.5 mm
Cutting edge $\varnothing D_c$	6 mm
Shank $\varnothing D_s$	6 mm
No. of teeth $Z$	4
Overall length $L$	65 mm
Recess $\varnothing D_1$	5.2 mm
Programming radius	1 mm
Feed $f_z$ in steel < 60 HRC	0.088 mm

Overhang length $L_1$ incl. recess	20 mm
Setting angle $\kappa$	6 degrees
Series	Diabolo
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal $\varnothing$	h9
Helix angle	12 degrees
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Shank	DIN 6535 HA to h5
Through-coolant	no
Machining strategy	HPC
Colour ring	red
Type of product	End torus mill

## User data

	Suitability	$V_c$	ISO code
Steel < 1400 N/mm <sup>2</sup>	suitable	190 m/min	P
Steel < 50 HRC	suitable	170 m/min	H
Steel < 55 HRC	suitable	150 m/min	H
Steel < 60 HRC	suitable	110 m/min	H
Steel < 65 HRC	suitable	80 m/min	H
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		

Air  
**Services**

suitable

Shank grinding Type HB

129100 HB