

**Garant**
**Burr Z9 very coarse (NF/Alu), Carbide, Type: C1225**

**Order data**

Order number	540709 C1225
GTIN	4045197522481
Item class	51D

**Description**
**Version:**

 Shank  $\varnothing$  6 mm.

**GARANT** burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Shape C cylindrical ball nose** (WRC).

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

 Shank  $\varnothing$ : 6 mm

Shape description: ball nose

 Head  $\varnothing$ : 12 mm

Head length: 25 mm

Overall length: 65 mm

 Shank  $\varnothing$ : 6 mm

**Technical description**

Tooth type abbreviation	Z9
Toothing grit designation	very coarse (NF/Alu)
Head $\varnothing$	12 mm
Shape	C1225
Shape description	ball nose
Overall length	65 mm

Shank Ø	6 mm
Head length	25 mm
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		