

uvex

Comfort safety glasses uvex pheos, Size: NORMAL



Order data

Order number	096524 NORMAL
GTIN	4031101538808
Item class	04U

Description

Version:

Modern fashion-look safety glasses with uvex supravision excellence coating: scratch resistant, free of condensation and resistant to chemicals. The metal-free glasses have a **wide field of view, without frames**, so that the eyes are well protected, even in the side areas. **Distortion-free viewing** through duo-spherical lenses, without tiring the eyes. Open frame concept for better **ventilation**. Available in **2 different widths** for optimum fit.

Standard:

EN 166; EN 170

Frame properties: Side padding

Lens coating: scratch-resistant

Lens coating: resistant to chemicals

Lens coating: free of condensation

UV protection: UV400

Lens material: Polycarbonate

Lens identification: 2C-1.2 W 1 FKN

Technical description

Glasses size	Normal
Lens coating	scratch-resistant
Lens coating	resistant to chemicals
Lens coating	free of condensation
Lens material	Polycarbonate

Lens identification	2C-1.2 W 1 FKN
UV protection	UV400
Series	pheos
Frame identification	W 166 FT CE
Frame properties	Side padding
Type of product	Safety glasses

Accessories

Storage box	096920
Storage box	096921
Storage box	096910
Lens cleaning towelettes 100 pieces	096690
Glasses case Type	096930
Retaining strap with width adjustment	096940
Wall attachment bracket for moist lens cleaning towelettes	096691
Glasses cleaning station	096694
Glasses case Type CASE	096932 CASE