

## Garant

**GARANT Power Tang 90° tangential high-performance shoulder mill, with bore, Ø D / number of effective cutting edges Z: 63/8mm**



### Order data

Order number	215122 63/8
GTIN	4045197861412
Item class	210

### Description

#### Version:

Maximum stability due to tangentially arranged inserts. High feed rate values for maximum metal removal rate due to optimum indexable insert with stability in the direction of the cutting force.

#### Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.0** with bit No. **674252 size 15IP**.

### Technical description

Cutting edge Ø D <sub>c</sub>	63 mm
Pack of insert screws	219882 (15IP; 3.0 Nm)
Overall length L <sub>tot</sub>	40 mm
maximum cutting depth a <sub>p,max</sub>	12 mm
Mounting bore Ø	27 mm
suitable indexable insert	LO.. 130708

Number of cutting edges Z	8
Series	Power Tang
Shank type	with bore
Setting angle $\kappa$	90 degrees
Milling application	Corner milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

---

## Accessories

Torque screwdriver, fixed setting set torque 3,0 N·m	211750 3,0
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Pack of insert screws 10 pieces	219882